

本机特点: (Features)

型号 (Type)	粘接托槽时间(Binding time)	粘接效果 (Effect)	患者体验 (patient feedback)
LED.H 正畸 LED.H Ortho	3 秒/照射面 3 sec/side	牢固 (solid)	无灼痛感 (no pain)
普通光固化机 Normal curing light	20 秒/照射面 20sec/side	无保障 Unguaranteed	牙齿灼痛 (painful)

对比情况: 啄木鸟 LED.H 正畸光固化机粘接托槽效率更高, 效果更好, 患者体验更舒适。



Comparison: Woodpecker LED.H ortho is more efficient in binding the ortho bracket with better effect and patient feedback.

技术特点:

Technical features:

1、为正畸专业调试光源, 散热好, 机身小巧, 能够长时间使用。

1. Adjusted light source for ortho, good cooling with slim body, which can be used for a long time.

2、两种档位, 同时具备正畸和普通光固化机功能。

2. 2 modes available: ortho and normal.